

E1512-70

Chloramine Resistant Sealing Material (EPDM)



Excellent Resistance:

Parker's E1512-70, chloramine resistant ethylene propylene, offers improved resistance to chloramine degradation and swelling providing a significantly longer seal life. This improvement can reduce potential warranty claims when used in plumbing fixtures and potable water handling equipment where chloramine is present.

The Need For Change:

As technology advances, we change and promote a safer, more efficient way to live. This progression however, directly effects existing standards and methods, forcing them to acclimate to a new environment, creating a new industry need.



Contact Information:

Parker Hannifin Corporation
O-Ring Division
2360 Palumbo Dr.
Lexington, KY 40509

phone 859 269 2351
fax 859 335 5128
email@parker.com

www.parker.com

Product Features:

- Internally Lubed; providing low friction
- Zero degradation and minimal swelling in chloramine and chlorine
- Low compression set
- Compound is globally available
- NSF approved



ENGINEERING YOUR SUCCESS.

E1512-70

In the consumer industry, water treatments facilities are using chloramine as a primary means to disinfect potable water in lieu of free chlorine. Chloramine is less reactive to organic material in water than chlorine, therefore producing much lower concentrations of disinfection by-products (which may have adverse health effects at high levels) in the distribution system. Chloramine also provides better protection against bacterial re-growth in systems with large storage tanks and dead-end water mains.

On the downside, chloramines are more aggressive to elastomers than free chlorine at equivalent concentrations. Existing seal materials can be attacked by chloramine, causing degradation, disintegration, and swelling. These property changes can cause seal failure, creating performance issues and warranty claims for water handling equipment manufactures.

The standard ASTM D6284 test for rubber properties was conducted on NSF-certified elastomer compounds, including existing Parker formulations, new Parker chloramine-resistant formulations, and competitor formulations. Based on the test results, Parker's chloramine-resistant materials will provide significantly longer useful seal life compared to all others tested

Test Report on Compound E1512-70 to M3DA 710 A26 B36 EA14 F19 G11 G21 Z1		
Z1 = Elongation at Break = 150% min		
Z2 = Compression Set on O-Rings: 70 hrs @ 150°C		
	Compound E1512-70	Spec.
Originals		
Hardness, Durometer, Shore 'A', points	72	70+/-5
Tensile Strength, Mpa	13.3	10 min
Elongation, % (Z1)	205	150 min
Heat Aged 70 hrs @ 150°C		
Change in Hardness, pts	+2	+10 max
Change in Tensile Strength, %	-10	-20 max
Change in Elongation, %	+7	-20 max
Compression Set 22 hrs @ 150°C		
Compression Set, % (Plied Slabs)	10	25 max
Compression Set 70 hrs @ 150°C on O-Rings (Z2)		
1.78 mm C/S	34	45 max
2.62 mm C/S	34	45 max
3.53 mm C/S	32	45 max
5.33 mm C/S	32	45 max
Aging in Distilled Water 70 hrs @ 100°C		
Change in Volume, %	+4.8	+/-5
Tear Strength		
Die 'B' (kN/m)	33	17 min
Die 'C' (kN/m)	25	17 min
Low Temperature Brittleness		
Non-Brittle after 3 min @ -55°C	Pass	Pass
Chloramine resistance: 50 ppm Chloramine Solution Aged (Masco D6284) @ 70°C for 3 weeks **		
Change in Volume, %	6	record
Change in Hardness, pts	0.4	record
Chloramine resistance: 50 ppm Chloramine Solution Aged (ASTM D6284) using 25 x 50 x 1.02 mm test slab @ 70°C for 8 weeks **		
Change in Volume, %	24	record
Change in Hardness, pts	-5	record
Chlorine resistance: 50 ppm Chlorine Solution Aged (ASTM D6284) using 25 x 50 x 1.02 mm test slab @ 70°C for 8 weeks **		
Change in Volume, %	16.8	record
Change in Hardness, pts	-4.6	record

**Testing performed by third party

Tests performed on ASTM type specimen
Values may be different for other type specimen

